






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.2.28	阿树



Connector Chimerism(Reference)




PCB LAYOUT

PART NO.:

X4001 W M-02-LP SN
① ② ③ ④ ⑤ ⑥

- ①Series Number.
②Category:W-Wafer
③Category:M-Male
④Row No.-Pin No.:02 PIN
⑤Material:LP-LCP 94V-0
⑥Plating Category:SN-Tin Plating

Specifications:
规格:
Voltage rating:300V AC/DC
额定电压: 300V AC/DC
Current rating:3A AC/DC
额定电流: 3A AC/DC
Withstanding voltage:1700V AC/minute
耐受电压: 1700V AC/分钟
Temperature range:-40℃-+105℃
温度范围: -40℃-+105℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:20mΩ Max
接触电阻: 20mΩ Max



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



X4001WF-02-LPSN		LCP	Phosphor Bronze	X4001WF
PART NO		Material	Material	Suitable XKB Female
DESIGN	阿树	VIEW:	MODEL TYPE: 4.0mm BTB Connector	
CHECKED		UNIT: mm/in	PART NO.: X4001WM-02-LPSN	
APPROVED		SIZE: A4	DWG NO.:	

SCALE	PAGE	REVISION
N/A	1/1	A1