






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A			2024.09.02	
A2	ECN-P-2026032702			2026.03.27	



SEC:A-A



SEC:B-B

Current rating:25A AC/DC
25A AC/DC
Temperature range:-40°C~+125°C
-40°C~+125°C

PART NO.:

K828801 I-P SN

- 1.K:XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:T-Terminal
- 4.Material:Phosphor Bronze
- 5.Plating:SN-Plated Tin

K828801T-PSN	Phospho Bronze	AWG#13-17	K828801H
PART NO	Material	Wire Range	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	
CHECKED	
APPROVED	

VIEW: 
UNIT: mm/in
SIZE: A4

MODEL TYPE: 5.0mm Automobile Connectors
PART NO.: K828801T-PSN
DWG NO.: