





Specifications

- $V_{o l t a g e}$ rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000M \Omega$
- Contact resistance: $\leq 10m \Omega$
- After environmental testing : $\leq 20m \Omega$

X3025 W V X-2x10 -46SN
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series No.
- ② Category : W-W AFER
- ③ Weld in 9 Board Angle : $\sqrt{S}$ straight 180°
- ④ Welding Way: Blank-DIP
- ⑤ Row No.-Pin No.: 2*XX-2*01P~2*22P
- ⑥ Plug the Pin & Special No.:
- ⑦ Material: 66-PA66 94V-0 ;PT-PBT 94V-0;
- ⑧ 46-PA46 94V-0 LP-LCP 94V-0
- ⑨ Plating Category: SN-Bright Tin Plating;
- V01-All Gold Flash
- ⑩ Color : Blank-Natural Color



X3025 WV-2x10-46V01	PA 46 UL 94V-0	Brass	Tin-Plated	X3025H
X3025WV-2x10-LPSN	LC P UL 94V-0			
X025 WV-2x10-66SN	PA 66 UL 94V-0			
X3025 WV-2x10-46SN	PA 46 UL 94V-0			
X3025WV-2x10-PTSN	PBT UL 94V-0			
PART NO	Material	Mate rial(Pin)	Finish(Pin)	Mate s With XK B Housing

Poles	D _i dimensions (mm)		Poles	D _i dimensions (mm)	
	A	B		A	B
2*01	---	6.65	2*07	18.00	24.65
2*02	3.00	9.65	2*08	21.00	27.65
2*03	6.00	12.65	2*09	24.00	30.65
2*04	9.00	15.65	2*10	27.00	33.65
2*05	12.00	18.65	2*11	30.00	36.65
2*06	15.00	21.65	2*12	33.00	39.65

DSND		DATE		SCALE: N/A	MODEL TYPE: 3.00 mm Crimp Style Connectors
DWN		DATE		VIEW:	PART NO.: X3025WV- 2x10-46SN
CHKD		DATE		UNIT: mm/in	DWG NO.: X-X3025WV- 2x10-46SN
APPD		DATE		SIZE: A4	WEIGHT 1.0g
XKB INDUSTRIAL PRECISION CO.,LIMITED					SHEET 1/1
					REVISION A0

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX				XKB	ANGULAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5

REVISIONS

www.helloxkb.com