






Specifications:

规格:

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:5A AC/DC

额定电流: 5A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-40℃-+125℃

温度范围: -40℃-+125℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ min

Contact resistance:20mΩ max

接触电阻: 20mΩ max

X4140 H M - 2x03 - N0

① ② ③ ④ ⑤

1.Series No

2.Category:H-Housing

3.Housing Type:M-Male Housing

4.Row No,Pin No:2xXX-2x02~2x03P

5.Material:N0-PA66 94V-0

Poles	Dimensions(mm)	
	A	B
2x02	4.14	10.36
2x03	8.28	14.50

X4140HM-2x03-N0	PA66	X4140W	X4140HF	X4140TF
PART N0	Material	Suitable XKB Wafer	Suitable XKB Housing	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 4.14mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X4140HM-2x03-N0		
CHKD		UNIT: mm/in	DWG NO.: X-X4140HM-2x03-N0		
APPD		SIZE: A4			
L PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED