





07~09 Pin



10~16 Pin

Specifications:

规格:
Voltage rating:100V AC/DC
 额定电压: 100V AC/DC
Current rating:3A AC/DC
 额定电流: 3A AC/DC
Withstanding voltage:800V AC/minute
 耐受电压: 800V AC/分钟
Temperature range:-25℃~+85℃
 温度范围: -25℃~+85℃
Insulation resistance:1000MΩ min
 绝缘电阻: 1000MΩ Min
Contact resistance:20mΩ Max
 接触电阻: 20mΩ Max

X2000	W	V	- 16	- N0	SN
①	②	③	④	⑤	⑥

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Stright 180°
- 4.Row No.Pin No:XX-02~16P
- 5.Material:N0-PA66 UL94V-0
- 6.Plating:SN-Tin Plated

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.00	6.00	08	14.00	18.00
03	4.00	8.00	09	16.00	20.00
04	6.00	10.00	10	18.00	22.00
05	8.00	12.00	11	20.00	24.00
06	10.00	14.00	12	22.00	26.00
07	12.00	16.00	16	30.00	34.00

X2000WV-16-N0SN	PA66	Brass	X2000H
PART N0	Material	Material(Pin)	Suitable XKB Housing

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS						UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X2000WV-16-N0SN		
CHKD		UNIT: mm/in	DWG NO.: X-X2000WV-16-N0SN		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0