




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A			2025.06.04	
A2	N/A			2026.04.16	

Specifications()

- 1.Voltage rating():DC 12V
- 2.Current rating():0.5A AC/DC
- 3.Withstanding voltage():≥ 250V AC/minute
- 4.Insulation resistance():≥ 100MΩ Min
- 5.Contact resistance():≤100mΩ Max
- 6.Operating force():±50gf
- 7.Travel 0.35±0.15mm
- 8.Temperature range(): -40 ~+85




PCB MOUNTING HOLES



CIRCUIT DIAGRAM

PAPT NO	TS-1145A-D-B
Operating Force	D:350gf
Height	H:2.5
Keystake	B:Silica gel

E	Button	1	Silicone	Blue
D	Cover	1	Phosphor bronze	Copper-tin plating
C	Shrapnel	1	SUS	Ag-Plating
B	Pedestal	1	LCP	White
A	Terminal	1	Phosphor bronze	Ag-Plating
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE: TACT SWITCH
CHECKED		UNIT: mm/in	PART NO.: TS-1145A-D-B
APPROVED		SIZE: A4	DWG NO.: