








由 AUTODESK 学生版生成




Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2*01	---	5.60	2*07	25.20	30.80
2*02	4.20	9.80	2*08	29.40	35.00
2*03	8.40	14.00	2*09	33.60	39.20
2*04	12.60	18.20	2*10	37.80	43.40
2*05	16.80	22.40	2*11	42.00	47.60
2*06	21.00	26.60	2*12	46.20	51.80




2*1P




2*2P



2*3P



2*4P



2*5P



2*6P

Specifications:

规格:

XKB

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:9A AC/DC

额定电流: 9A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤10mΩ

接触电阻: ≤10mΩ

After environmental testing:≤20mΩ

环境测试后: ≤20兆欧

X9357 H F -2x01 G-N2

① ② ③ ④ ⑤ ⑥ ⑦

① Series No.

② Category:H-HSG

③ Welding Board Angle:F-Female

④ Row No.-Pin No.:2*XX-2*01P~2*12P

⑤ Plug the Pin & special No.:

I-Without the Wing; G-With the Wing

⑥ Material:N0-PA66 94V-0:N2-PA66 94V-2

⑦ Color:Blank-Natural Color BK-Black



X9357HF-2x01-N2BK	Nylon 66 94V-2 Black	X9357TM	X9357W Or 9357H	Without Ears
X9357HF-2x01G-N2	Nylon 66 94V-2			With Ears
X9357HF-2x01I-N2	Nylon 66 94V-2			Without Ears
X9357HF-2x01G-N0	Nylon 66 94V-0			With Ears
X9357HF-2x01I-N0	Nylon 66 94V-0			Without Ears
PART NO	Material	Suitable XKB Terminal	Suitable XKB Housing	Note

					XKB	ANGLAR	±5°	DWN		DATE		VIEW: 	2.40mm Crimp Style Connectors			
Δx						L ≤ 4	±0.2	CHKD		DATE		UNIT: mm/in	PART NO.: X9357HF-2x01G-N2			
Δx						4<L ≤ 16	±0.3				DATE					
Δx						16<L ≤ 63	±0.4	APPD		DATE		SIZE: A4	DWG NO.: X-X9357HF-2x01G-N2			
MARK	DESCRIPTION			DATE	REVISED	APPROVED	L > 63		±0.5			DATE				
REVISIONS						UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT	SHEET	REVISION
www.helloxkb.com														1.0g	1/1	A0