



	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.19	阿树



4	STATOR	BRASS	35	34.00	36.10	37.00	39.90	2
3	TERMINAL	PHOSPHOR BRONZE						POSITION
2	COVER	ERMOPLASTIC UL94V-0	BLACK					1
1	HOUSING	THERMOPLASTIC UL94V-0	NATURAL					1
NO	COMPONENTS	MATERIALS	FINISH/COLOR	SPECIFICATION				QUANTITY

DESIGN	阿树	VIEW:		MODEL TYPE:	FPC CONNECTOR
CHECKED		UNIT:	mm/in	PART NO.:	X10A20L20G
APPROVED		SIZE:	A4	DWG NO.:	X10A20L20G
PRECISION CO., LIMITED				SCALE	PAGE
				N/A	1/1
				REVISION	A1

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XKLB 星城 Connection

XKB INDUSTRIAL PRECISION CO.,LIMITED

X10A20L20G		
SCALE	PAGE	REVISION
N/A	1/1	A1