





- Voltage rating: 250V AC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000M\ \Omega$
- Contact resistance: $\leq 20m\Omega$
- After environmental testing : $\leq 30m\Omega$

X2012 W R-05- N0 SN

①	②	③	④	⑤	⑥
---	---	---	---	---	---

① Series No.

② Category : W-WAFER

③ Wedding Board Angle : R-Stright 90°

④ Row No.-Pin No.: XX-02P~15P

⑤ Material : N0-PA66 94V-0

⑥ Plating Category: Sn-Bright

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	6.00	5.20	10	18.00	22.00	21.20
03	4.00	8.00	7.20	11	20.00	24.00	23.20
04	6.00	10.00	9.20	12	22.00	26.00	25.20
05	8.00	12.00	11.20	13	24.00	28.00	27.20
06	10.00	14.00	13.20	14	26.00	30.00	29.20
07	12.00	16.00	15.20	15	28.00	32.00	31.20
08	14.00	18.00	17.20				
09	16.00	20.00	19.20				

X2012WR-Q5-N0SN	Nyoln 66 UL 94V-0	Brass	Tin-Plated	X2012H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connectors
ΔX					ANGULAR	$\pm 5^\circ$	DWN		DATE		VIEW: 	PART NO.:
ΔX					$L \leq 4$	± 0.2	CHKD		DATE		UNIT: mm/in	X2012WR-05-N0SN
ΔX					$4 < L \leq 16$	± 0.3	APPD		DATE		SIZE: A4	DWG NO.:
MARK	DESCRIPTION	DATE	REVISED	APPROVED	$16 < L \leq 63$	± 0.4						X2012WR-05-N0SN
					$L > 63$	± 0.5						
REVISIONS							UNSPECIFIED TOLERANCES					
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn							XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g
												SHEET 1/1
												REVISION A0