







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图面升级整理图面	2025.2.13	阿树
A2	N/A	(A2)X4	产品尺寸修正	2025.09.17	阿树



X方向浮动量/X Directio :±0.7mm




Y方向浮动量/Y Directio :±0.7mm



Specifications:
规格:
Voltage rating:50V AC/DC
额定电压: 50V AC/DC
Current rating:0.5A AC/DC
额定电流: 0.5A AC/DC
Withstanding voltage:200V AC/minute
耐受电压: 200V AC/分钟
Temperature range:-40℃~+125℃
温度范围: -40℃~+125℃
Insulation resistance:500MΩ Max
绝缘电阻: 500MΩ Max
Contact resistance:20mΩ Max
接触电阻: 20mΩ Max

PART NO.:
X0635 F V S-60 C S-LP V01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨
①Series No
②Category:F-Female
③Welding Board Angle:V-Stright 180°
④Welding Way: S-SMT
⑤Row No.Pin No:XX-20~100P
⑥Height:C=15.0mm, Mating height 15.0±0.5
⑦Special No:S-With positioning column
⑧Material:LP-LCP UL94V-0
⑨Plating:V01-Gold paltd 4u" MIN

Poles	Dimensions(mm)				
	A	B	C	D	E
20	11.950	10.550	5.715	8.150	8.150
30	15.125	13.725	8.890	11.325	11.325
40	18.300	16.900	12.065	14.500	14.500
50	21.475	20.075	15.240	17.675	17.625
60	24.650	23.250	18.415	20.850	20.850
70	27.825	26.425	21.590	24.025	24.025
80	31.000	29.600	24.765	27.200	27.200
90	34.175	32.775	27.940	30.375	30.375
100	37.350	35.950	31.115	33.550	33.550



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



X0635FVS-60CS-LPV01		LCP	Phosphor Bronze	X0635W
PART NO		Material	Material(Pin)	Suitable XKB Wafer
DESIGN	阿树	VIEW:	UNIT: mm/in	MODEL TYPE: 0.635mm BTB Connector
CHECKED		SIZE: A4		PART NO.: X0635FVS-60CS-LPV01
APPROVED				DWG NO.: X-X0635FVS-60CS-LPV01
SCALE			PAGE	REVISION
N/A			1/1	A2