







Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/ 分钟

Temperature range:-25 ℃ -+85℃

温度范围: -25℃ -+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤30mΩ

接触电阻: ≤30mΩ

After environmental testing:≤40mΩ

环境测试后: ≤40兆欧

X2011 W V S-04 A- 9T SN

① ②③④⑤⑥⑦ ⑧ ⑨

1.Series No

2.Category:W-WAFER

3.Welding Board Angle:V-Straight 180°

4.Welding Way:S-SMT

5.Row No-Pin No:XX-02P~16P

6.Plug the Pin&Special No:A-With Located Block

7.Material:9T:PA9T UL 94V-0

8.Plating Category:SN-Bright Tin Plating

9.Color:Blank-Natural Color

poles	Dimensions(mm)		poles	Dimensions(mm)	
	A	B		A	B
2	2.00	8.00	10	18.00	24.00
3	4.00	10.00	11	20.00	26.00
4	6.00	12.00	12	22.00	28.00
5	8.00	14.00	13	24.00	30.00
6	10.00	16.00	14	26.00	32.00
7	12.00	18.00	15	28.00	34.00
8	14.00	20.00	16	30.00	36.00
9	16.00	22.00			

X2011WVS-04A-9TSN	PA9T UL 94V-0	Brass	Phosphor Bronze	Tin-Plated	X2011H-A
PART NO	Material	Material(pin)	Material(Solder Tab)	Finish(Pin and Solder tab)	Suitable XKB Housing

Wire to board connector

DSND		DATE		SCALE: N/A	MODEL TYPE: 2.00mm Crimp Style Connectors
DWN		DATE		VIEW:	PART NO.: X2011WVS-04A-9TSN
CHKD		DATE		UNIT: mm/in	DWG NO.: X-X2011WVS-04A-9TSN
APPD		DATE		SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g
					SHEET 1/1
					REVISION A0

					units: mm
Δx					tolerance:
Δx					X.X ±0.2mm
Δx					X.XX ±0.1mm
MARK					X.XXX ±0.05mm
REVISIONS					UNSPECIFIED TOLERANCES
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn					