









Recommended PCB Layout
Tolerance: ± 0.05



Specifications:

规格:

Voltage rating: 100V AC/DC

额定电压: 100V AC/DC

Current rating: 1.5A AC/DC

额定电流: 1.5A AC/DC

Withstanding voltage: 500V AC/minute

耐受电压: 500V AC/分钟

Temperature range: -40°C ~ $+105^{\circ}\text{C}$

温度范围: -40°C ~ $+105^{\circ}\text{C}$

Insulation resistance: $\geq 500\text{M}\Omega$

绝缘电阻: $\geq 500\text{M}\Omega$

Contact resistance: $\leq 20\text{m}\Omega$

接触电阻: $\leq 20\text{m}\Omega$

X1515	W	V	S	2x05	-LP	SW
①	②	③	④	⑤	⑥	⑦

1. Series No

2. Category: W-Wafer

3. Welding Board Angle: V-Stright 180°

4. Welding Way: S-SMT

5. Row No. Pin No: 2xXX-2x04~2x14P

6. Material: LP-LCP UL94V-0 (Natural)

7. Plating: SW- Matte Tin Plated

Poles	Dimensions (mm)			
	A	B	C	D
2x04	4.50	10.30	8.50	8.95
2x05	6.00	11.80	10.00	10.45
2x06	7.50	13.30	11.50	11.95
2x07	9.00	14.80	13.00	13.45
2x08	10.50	16.30	14.50	14.95
2x09	12.00	17.80	16.00	16.45
2x10	13.50	19.30	17.50	17.95
2x11	15.00	20.80	19.00	19.45
2x12	16.50	22.30	20.50	20.95
2x13	18.00	23.80	22.00	22.45
2x14	19.50	25.30	23.50	23.95

X1515WVS-2x05-LPSW	LCP	Phosphor Bronze	X1515H-A
PART N0	Material	Material (Pin)	Suitable XKB Housing

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

XKB INDUSTRIAL PRECISION CO., LIMITED

DSND		SCALE: N/A	MODEL TYPE: 1.5mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X1515WVS-2x05-LPSW		
CHKD		UNIT: mm/in	DWG NO.: X-X1515WVS-2x05-LPSW		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0