

1

2

3

4

A

A

B

B

C


C

D

D

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.04	阿树

SPECIFICATION
Contact Rating: 50mA,12V DC
Contact Resistance: 100mΩ max
Insulation Resistance: 100MΩ min,500V DC
Dielectric Strength: 250V AC/1minute
Travel: 0.25mm
Operating Temp: -30℃~+85℃
Storage Temp: -30℃~+80℃



PAPT NO	TS-1159B-B-B-W
Operating Force	A:100gf B:160gf C:260gf D:320gf E:400gf
Height	H: A:3.4 B:4.2 C:4.8 D:5.1
Color	BL:blue W:white

⑤	Terminal	4	Brass (0.30t)	Plating silvering
④	Contact	1	F.ag/SUS	Natural
③	Base	1	PA46	
②	Cover	1	SPSS	Plating Nickel
①	Keystake	1	Silica gel	

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN
CHECKED
APPROVED

阿树

VIEW:
UNIT: mm/in
SIZE: A4

MODEL TYPE: TACT SWITCH		
PART NO.: TS-1159B-B-B-W		
DWG NO.: TS-1159B-B-B-W		
SCALE	PAGE	REVISION
N/A	1/1	A1

1

2

3

4