





#### Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:24A AC/DC

额定电流: 24A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-40℃~+105℃



温度范围: -40℃~+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ


Contact resistance:≤20mΩ

接触电阻: ≤20mΩ



X9396 W V - 02 R - LP SN  
① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Stright 180°
- 4.Row No.Pin No:XX-02~2x08Pin
- 5.Special No:R-DIP 2.2mm
- 6.Material:LP-LCP UL94V-0 ,Natural  
CAP:LCP UL94V-0 ,Natural
- 7.Plating:SN- Tin Plated



Recommended PCB Layout(Top view)  
Tolerance:±0.05mm

| Poles | Dimensions (mm) |       |       |
|-------|-----------------|-------|-------|
|       | A               | B     | C     |
| 02    | 3.96            | 7.92  | 5.32  |
| 03    | 7.92            | 11.88 | 9.28  |
| 04    | 11.88           | 15.84 | 13.24 |
| 05    | 15.84           | 19.80 | 17.20 |
| 06    | 19.80           | 23.76 | 21.16 |
| 07    | 23.76           | 27.72 | 25.12 |
| 08    | 27.72           | 31.68 | 29.08 |

|                  |          |               |                      |
|------------------|----------|---------------|----------------------|
| X9396WV-02R-LPSN | LCP      | Brass         | X9396H               |
| PART NO          | Material | Material(Pin) | Suitable XKB Housing |

|                                                   |             |      |         |          |                        |      |
|---------------------------------------------------|-------------|------|---------|----------|------------------------|------|
|                                                   |             |      |         |          | ANGLAR                 | ±5°  |
| ΔX                                                |             |      |         |          | L≤ 4                   | ±0.2 |
| ΔX                                                |             |      |         |          | 4<L≤ 16                | ±0.3 |
| ΔX                                                |             |      |         |          | 16<L≤ 63               | ±0.4 |
| MARK                                              | DESCRIPTION | DATE | REVISED | APPROVED | L> 63                  | ±0.5 |
| REVISIONS                                         |             |      |         |          | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com   www.helloxkb.cn   www.xk-dg.cn |             |      |         |          |                        |      |

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

|      |             |                                             |          |
|------|-------------|---------------------------------------------|----------|
| DSND | SCALE: N/A  | MODEL TYPE:<br>3.96mm Crimp Style Connector |          |
| DWN  | VIEW:       | PART NO.:<br>X9396WV-02R-LPSN               |          |
| CHKD | UNIT: mm/in | DWG NO.:<br>X-X9396WV-02R-LPSN              |          |
| APPD | SIZE: A4    | WEIGHT                                      | SHEET    |
|      |             |                                             | REVISION |
|      |             | 1/1                                         | A0       |