







Specifications:

规格:

Voltage rating:50V AC/DC

额定电压: 50V AC/DC

Current rating:0.8A AC/DC

额定电流: 0.8A AC/DC

Withstanding voltage:250V AC/minute

耐受电压: 250V AC/分钟

Temperature range:-25℃-+85℃

温度范围: -25℃-+85℃

X1004	W	V	S	-2x20	-9T	V01
①	②	③	④	⑤	⑥	⑦

- ① Series No.
② Category:W-WAFER
③ Wedding Board Angle:V-Stringht 180°
④ Welding way :S-SMT
⑤ Row No.Pin No.: 2xXX
⑥ Material:9T-PA9T 94V-0
⑦ Plating Category:V01-Gold Flash

PIN	DIM A	DIM B	DIM C	DIM D
2X10P	9.00	12.30	10.45	11.25
2X15P	14.00	17.30	15.45	16.25
2X20P	19.00	22.30	20.45	21.25
2X25P	24.00	27.30	25.45	26.25

							DSND		DATE		SCALE: N/A	MODEL TYPE: 1.0 mm Crimp Style Connector
							DWN		DATE		VIEW:	PART NO.: X1004WVS-2x20-9TV01
							CHKD		DATE		UNIT: mm/in	DWG NO: X-X1004WVS-2x20-9TV01
							APPD		DATE		SIZE: A4	WEIGHT 1.0g
							XKB INDUSTRIAL PRECISION CO.,LIMITED					SHEET 1/1
												REVISION A0