

Specifications:

Voltage rating:150V AC/DC

额定电压: 150V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-25°C-+85°C


温度范围: -25℃-+85℃

Insulation resistance: $\geq 500 \text{ M}\Omega \text{ min}$

绝缘电阻: $\geq 500\text{M}\Omega$ Min

Contact resistance: $\leq 30\text{m}\Omega$ Max

接触电阻: $\leq 30\text{m}\Omega$ Max



P.C.B LAYOUT

X9812	W	V	S	-2x05	-6T	V01
(1)	(2)	(3)	(4)	(5)	(6)	(7)

- 1.Series No
2.Category:W-Wafer
3.Welding Board Angle:V-Stright 180°
4.Welding Way:S-SMT
5.Row No.Pin No:XX-2x05~2x25P
6.Material:6T-PA6T UL 94V-0 Natural
CAP:6T UL 94V-0 Natural
7.Plating:V01-Gold Flash

Poles	Dimensions(mm)	
	A	B
2x02	1.25	8.75
2x05	5.00	12.50
2x06	6.25	13.75
2x07	7.50	15.00
2x10	11.25	18.75
2x12	13.75	21.25
2x15	17.50	25.00
2x20	23.75	31.25

X9812WVS-2x05-6TV01	PA6T	Brass	X9812H
PART N0	Material	Material(Pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 1.25mm Crimp Style Connector
DWN		VIEW: 	PART NO.: X9812WVS-2x05-6TV01
CHKD		UNIT: mm/in	DWG NO.: X-X9812WVS-2x05-6TV01
APPD		SIZE: A4	

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0