

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.02.29	

Specifications (规格):

1. Voltage rating (额定电压): 50V AC DC
2. Current rating (额定电流): 2.4A AC/DC
3. Withstanding voltage (耐压值): $\geq 500V$ AC/minute
4. Insulation resistance (绝缘电阻): $500M\Omega$ Min
5. Contact resistance (绝缘电阻): $20m\Omega$ Max
6. Temperature range (使用温度): $-25^{\circ}C \sim +85^{\circ}C$

PART NO.:

X1502 W R-04 K-N0 SN
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No
- ② Category: W-Wafer
- ③ Welding Board Angle: R-Straight 90°
- ④ Row No-Pin: XX-02P~15P
- ⑤ Plug The Pin&Special NO: K-Kink
- ⑥ Material: N0-PA66 UL94V-0
- ⑦ Plating: SN-Bright Tin Plated

X1502WR-04K-N0SN	PA66 UL 94V-0	BRASS	TIN-PLATED	X1502H
PART NO.	MATERIAL	MATERIAL(PIN)	FINISH(PIN)	Suitable XKB Terminal

NUMBER OF POSITIONS	DIM.A	DIM.B	DIM.C	NUMBER OF POSITIONS	DIM.A	DIM.B	DIM.C
02	1.50	4.50	3.70	09	12.00	15.00	14.20
03	3.00	6.00	5.20	10	13.50	16.50	15.70
04	4.50	7.50	6.70	11	15.00	18.00	17.20
05	6.00	9.00	8.20	12	16.50	19.50	18.70
06	7.50	10.50	9.70	13	18.00	21.00	20.20
07	9.00	12.00	11.20	14	19.50	22.50	21.70
08	10.50	13.50	12.70	15	21.00	24.00	23.20

ANGULAR	$\pm 5^{\circ}$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XKB	DESIGN	桑 葚	VIEW: 	MODEL TYPE: 1.50mm Crimp Style Connector
	CHECKED		UNIT: mm/in	PART NO.: X1502WR-04K-N0SN
	APPROVED		SIZE: A4	DWG NO.: X-X1502WR-04K-N0SN
XKB INDUSTRIAL PRECISION CO.,LIMITED				SCALE: N/A
				PAGE: 1/1
				REVISION: A0