



PCB LAYOUT

Specifications:

规格:

Voltage rating: 250V AC/DC

额定电压: 250V AC/DC

Current rating: 1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage: 300V AC/minute

耐受电压: 300V AC/分钟

Temperature range: -40°C ~ +105°C

温度范围: -40°C ~ +105°C

Insulation resistance: ≥ 500MΩ

绝缘电阻: ≥ 500MΩ

Contact resistance: ≤ 20mΩ

接触电阻: ≤ 20mΩ

Material: PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category: 1U"Gold

镀层: 1U"Gold

Wave soldering temperature: 255 ± 5°C, 10S

波峰焊温度: 255 ± 5°C, 10S

X1311 F V - 03 - C43 D24
① ② ③ ④ ⑤ ⑥

1. Series No

2. Category: F-Female

3. Welding Board Angle: V-Straight 180°

4. Row No. Pin No: XX-02~40 Pin

5. Plastic height: C=4.3mm

6. Pin Length: D=2.4mm

X1311FV-03-C43D24	PA6T	Brass	X1311W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGULAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
ΔX					16 < L ≤ 63 ±0.4
ΔX					L > 63 ±0.5
REVISIONS					
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKLB

XKB INDUSTRIAL PRECISION CO., LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	1.27mm BTB Connector
CHKD	UNIT: mm/in	PART NO.: X1311FV-03-C43D24
APPD	SIZE: A4	DWG NO.: X-X1311FV-03-C43D24
		WEIGHT
		SHEET 1/1
		REVISION A0