





1

2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A			2025.2.24	



P.C.B LAYOUT

Specifications:

Voltage rating:250V AC/DC
250V AC/DC
Current rating:3A AC/DC
3A AC/DC
Withstanding voltage:1000V AC/minute
1000V AC/
Temperature range:-40 -+105
-40 -+105
Insulation resistance:≥1000MΩ
≥1000MΩ
Contact resistance:≤20mΩ
≤20mΩ
Material:PA6T UL94V-0
PA6T UL94V-0
Plating Category:1U"Gold
1U"Gold
Wave soldering temperature:255±5 10S
255±5 10S

PART NO.:

X4611 W R-XX I-C35 D28

Series No
Category:W-Wafer
Welding Board Angle:R-Stright 90°
Row No -Pin No:XX-02P-40P
Plastic height: l=2.0mm
Pin Length:C=3.5mm
Pin Length:D=2.8mm

X4611WR-XXI-C40D28	PA6T	Brass	X4611F
PART NO	Material	Material(Pin)	Suitable XKB Housing
DESIGN		VIEW:	MODEL TYPE: 2.0mm BTB Connector
CHECKED		UNIT: mm/in	PART NO.: X4611WR-XXI-C35D28
APPROVED		SIZE: A4	DWG NO.:
SCALE			PAGE
N/A			1/1
REVISION			A1

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

1

2

3

4