





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		产品尺寸变更, 图面升级整理图面	2024.11.18	阿树



SS13F06L10

L(MM)
2 ~ 10



RATING	0.3A 50V DC
CIRCUIT	1P3T
CONTACT RESISITANCE	100MΩ MAX
TRAVEL	3.2MM
OPERATING FORCE	250±100gf
OPERATING LIFE	10000

6	Spring	1	Steel wire	NATURAL
5	Teminal bass	1	Phenol resin	NATURAL
4	Knob	1	POM	G2-10
3	Contact clip	1	BSP	AG Plated
2	Terminal	4	BSP	AG Plated
1	Frame	1	SPCC	Ni Plated
NO	NAME	QTY	MATERIAL	Remark

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	SLIDE SEITCH
CHECKED		UNIT:	mm/in	PART NO.:	SS13F06L10
APPROVED		SIZE:	A4	DWG NO.:	