





P.C.B. LATOUT

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-40℃-+85℃

温度范围: -40℃-+85℃

Insulation resistance: 1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X8821 W V - 14 L - N0 SN
① ② ③ ④ ⑤ ⑥ ⑦

1. Series No.
2. Category:W-WAFER
3. Welding Board Angle: V-Straight 180°
- 4.Row No.Pin No.: XX-Single Row;
- 5.Plug the Pin&Special No:L-With Lock
- 6.Material:N0-PA66 94V-0
- 7.Plating Category: SN-Bright Tin Plating

Poles	A	B	C
02	2.50	7.50	5.80
03	5.00	10.00	8.30
04	7.50	12.50	11.00
05	10.00	15.00	13.50
06	12.50	17.50	16.00
07	15.00	20.00	18.50
08	17.50	22.50	21.00
09	20.00	25.00	23.50
10	22.50	27.50	26.00
11	25.00	30.00	28.50
12	27.50	32.50	31.00
13	30.00	35.00	33.50
14	32.50	37.50	36.00
15	35.00	40.00	38.50

X8821WV-14L-N0SN	Nylon UL 94V-0	Brass (Plating Tin)	X8821H-L	X8821T-L
PART NO	Material	Material(Pin)	Suitabke XKB Housing	Suitabke XKB Terminal

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
DESCRIPTION					DATE	REVISED
REVISIONS					APPROVED	UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.50mm Crimp Style Connectors		
DWN		VIEW: 	PART NO.: X8821WV-14L-N0SN		
CHKD		UNIT: mm/in	DWG NO.: X-X8821WV-14L-N0SN		
APPD		SIZE: A4			
L PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0