




R1 TYPE



R2 TYPE



PCB LAYOUT



PCB LAYOUT

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

Material:PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category:1U"Gold

镀层: 1U"Gold

Reflow soldering temperature:260±5℃, 10S

回流焊温度: 260±5℃, 10S

X6511 W V S - 07 H - C60 D48 R1
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1.Series No

2.Category:W-Wafer

3.Welding Board Angle:V-Straight 180°

4.Welding Way:S-SMT

5.Row No.Pin No:XX-02~40P

6..Plastic Height:H=2.5mm

7.Pin Length:C=6.0mm

8.Pin Length:D=3.0mm

9.Type:X-R1 ; R2

X6511WVS-07H-C60D48R1	PA6T	Brass	X6511F
PART NO	Material	Material(Pin)	Suitable XKB Female

ΔX	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					
ΔX					
ΔX					
MARK					
REVISIONS					
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	2.54mm BTB Connector
CHKD	UNIT: mm/in	PART NO.:
APPD	SIZE: A4	X6511WVS-07H-C60D48R1
		DWG NO.:
		X-X6511WVS-07H-C60D48R1
WEIGHT	SHEET	REVISION
	1/1	A0