




poles	Dimensions(mm)		poles	Dimensions(mm)		poles	Dimensions(mm)	
	A	B		A	B		A	B
2x02	2.54	5.08	2x13	30.48	33.02	2x24	58.42	60.96
2x03	5.08	7.62	2x14	33.02	35.56	2x25	60.96	63.50
2x04	7.62	10.16	2x15	35.56	38.10	2x26	63.50	66.04
2x05	10.16	12.70	2x16	38.10	40.64	2x27	66.04	68.58
2x06	12.70	15.24	2x17	40.64	43.18	2x28	68.58	71.12
2x07	15.24	17.78	2x18	43.18	45.72	2x29	71.12	73.66
2x08	17.78	20.32	2x19	45.72	48.26	2x30	73.66	76.20
2x09	20.32	22.86	2x20	48.26	50.80	2x31	76.20	78.74
2x10	22.86	25.40	2x21	50.08	53.34	2x32	78.74	81.28
2x11	25.40	27.94	2x22	53.34	55.88			
2x12	27.94	30.48	2x23	55.88	58.42			

X9555H-2x08E2-PT	PBT UL 94V-0	X9555T-A	X9555W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Wafer

						DSND		DATE		SCALE: N/A	MODEL TYPE: 2.54mm Crimp Style Connectors		
					units: mm	DWN		DATE		VIEW: 	PART NO.: X9555H-2x08E2-PT		
Δ X					tolerance:	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X9555H-2x08E2-PT		
Δ X					X.X ±0.2mm								
Δ X					X.XX ±0.1mm								
MARK	DESCRIPTION			DATE	REVISED	APPROVED	X.XXX ±0.05mm	APPD		DATE		SIZE: A4	
REVISIONS						XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT	SHEET	REVISION
UNSPECIFIED TOLERANCES											1.0g	1/1	A0
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn													