

Poles	Dimensions (mm)	
	A	B
2x01	8.35	
2x02	12.05	5.70
2x03	17.75	11.40
2x04	23.45	17.10
2x05	29.15	22.80
2x06	34.85	28.50

Specifications:

Voltage rating: 600V AC / DC

Current rating: 16A AC / DC

Withstanding voltage: 2200V AC/minute




Temperature range: -40°C~+105°C

Insulation resistance: $\geq 1000\text{M}\Omega$

Contact resistance: $\leq 2\text{m}\Omega$


After environmental testing : $\leq 10\text{m}\Omega$

Special No.: H-High conductive Brass




X5700 W R -2x01 -LP SW


- ① Series No.
② Category : W-WAFER
③ Welding Board Angle : R-Straight 90°
④ Row No.-Pin No.: 2xXX-2x02P~2x06P
⑤ Material: LP -LCP 94V-0
⑥ Plating Category: SW-Matte Tin Plating



2x03~2x06P



2x02P



2x01P

Recommended P.C.B Layout
General Tolerance±0.05

X5700WR-2x01-LPSW	High conductive Brass	X5700H	X5700T
PART NO	Material	Suitable XKB Housing	Suitable XKB Terminal

						DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector		
Δx					units: mm	DWN		DATE		VIEW: 	PART NO.: X5700WR-2x01-LPSW		
Δx					X.X ±0.2mm	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X5700WR-2x01-LPSW		
Δx					X.XX ±0.1mm	APPD		DATE		SIZE: A4			
MARK	DESCRIPTION				DATE	REVISED	APPROVED	X.XXX ±0.05mm					
REVISIONS						UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn											WEIGHT 1.0g	•SHEET 1/1	REVISION A0