


02P~04P Single Hole
Scale 1:0.7



X1503 W R S- 12 - 4T V01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- | Poles | Dimensions(mm) | | | |
|-------|----------------|-------|-------|-------|
| | A | B | C | D |
| 02 | 1.50 | 6.75 | 2.85 | |
| 03 | 3.00 | 8.25 | 4.35 | |
| 04 | 4.50 | 9.75 | 5.85 | |
| 05 | 6.00 | 11.25 | 7.35 | 3.00 |
| 06 | 7.50 | 12.75 | 8.85 | 3.00 |
| 07 | 9.00 | 14.25 | 10.35 | 4.50 |
| 08 | 10.50 | 15.75 | 11.85 | 6.00 |
| 09 | 12.00 | 17.25 | 13.35 | 7.50 |
| 10 | 13.50 | 18.75 | 14.85 | 9.00 |
| 11 | 15.00 | 20.25 | 16.35 | 10.50 |
| 12 | 16.50 | 21.75 | 17.85 | 12.00 |

DSND		SCALE: N/A	MODEL TYPE: Wire to Board Connector
DWN		VIEW:	PART NO.: X1503WRS-12-4TV01
CHKD		UNIT: mm/in	DWG NO.: X-X1503WRS-12-4TV01
APPD		SIZE: A4	

WEIGHT	SHEET	REVISION
	1/1	A0

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxb.com www.helloxb.cn www.xk-dg.cn						