








Specifications:

规格:

Voltage rating:350V AC/DC

额定电压: 350V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃--+105℃

温度范围: -40℃--+105℃

Insulation resistance:≥500MΩ

绝缘电阻: ≥500MΩ

Contact resistance:≤10mΩ

接触电阻: ≤10mΩ

X1511 H - 05 A - N0
① ② ③ ④ ⑤

- 1.Series No
- 2.Category:H-HSG
- 3.Special No:A-There are convex on both sides
- 4.Row No.Pin No:XX-02~11P
- 5.Material:N0-Nylon 66 UL94V-0 ;

Poles	Dimensions(mm)		
	A	B	C
02	1.50	3.55	4.40
03	3.00	5.05	5.90
04	4.50	6.55	7.40
05	6.00	8.05	8.90
06	7.50	9.55	10.40
07	9.00	11.05	11.90
08	10.50	12.55	13.40

X1511H-05A-N0	Nylon 66	X1511W-A	X1511T-A
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

					ANGLAR	±5°
Δ x					L≤ 4	±0.2
Δ x					4<L≤ 16	±0.3
Δ x					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE: 1.5mm Crimp Style Connector	
DWN	VIEW:	PART NO.: X1511H-05A-N0	
CHKD	UNIT: mm/in	DWG NO.: X-X1511H-05A-N0	
APPD	SIZE: A4	WEIGHT	SHEET
			REVISION
		1/1	A0