



AUTODESK 學生版生成 UNSPECIFIED TOLERANCES



无卤

⑦Plating Category: SW-Matte Tin



Poles	Dimension mm				Poles	Dimension mm			
	A	B	C	D		A	B	C	D
2	2.00	8.00	4.85	6.00	09	16.00	22.00	18.85	20.00
3	4.00	10.00	6.85	8.00	10	18.00	24.00	20.85	22.00
4	6.00	12.00	8.85	10.00	11	20.00	26.00	22.85	24.00
5	8.00	14.00	10.85	12.00	12	22.00	28.00	24.85	26.00
6	10.00	16.00	12.85	14.00	13	24.00	30.00	26.85	28.00
7	12.00	18.00	14.85	16.00	14	26.00	32.00	28.85	30.00
8	14.00	20.00	16.85	18.00	15	28.00	34.00	30.85	32.00

X2023WVS-09 -9TSW	PA9T UL 94V-0	Brass	Matte Tin	Phorpos Bronze	Matte Tin	X2023H
PART NO	Material	Material(Pin)	Finish(Pin)	Material (Soder Tabs)	Finish (Soder Tabs)	Mates With XKB Housing

							XKB	DSND		DATE		SCALE: N/A	MODEL TYPE: 2.0 mm Crimp Style Connectors
Δx				XKB	ANGLAR	$\pm 5^{\circ}$	DWN		DATE		VIEW: 	PART NO.: X2023WVS-09-9TSW	
Δx					$L \leq 4$	± 0.2	CHKD	DATE		UNIT: mm/in	DWG NO.: X-X2023WVS-09-9TSW		
Δx					$4 < L \leq 16$	± 0.3							
Δx					$16 < L \leq 63$	± 0.4	APPD	DATE		SIZE: A4			
MARK	DESCRIPTION	DATE	REVISED	APPROVED	$L > 63$	± 0.5							
REVISIONS							UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED				
www.helloxkb.com													
									WEIGHT	SHEET	REVISION		
										1/1	A0		