








REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图片面升级整理图面	2024.07.26	阿 树



SS13E05-L9


L(MM)
2~10

RATING	0.3A 50V DC
CIRCUIT	1P3T
CONTACT RESISTANCE	100MΩ MAX
TRAVEL	2.5MM
OPERATING FORCE	250±100gf
OPERATING LIFE	10000



4	Terminal	4	SUS		
3	Base	1	SUS		
2	Cover	1	SUS		
1	Keystone	1	PA66		
ITEM	PART NAME	TER.NO	QTY	MATERIAL	FINISHING

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿 树	VIEW:		MODEL TYPE:	SLIDE SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	SS13E05-L9
APPROVED		SIZE:	A4	DWG NO.:	X-SS13E05-L9