


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	(A1)X5	尺寸变更, 新增其他颜色卡位图面, 图面升级整理图面	2025.1.10	阿树

A






B

C


D




K776280WV-35-PTXXB




K776280WV-35-PTXXB
K776280WV-35-PTXXGY
K776280WV-35-PTXXC




K776280WV-35-PTXXW
K776280WV-35-PTXXBL




K776280WV-35-PTXXW



K776280WV-35-PTXXGY



K776280WV-35-PTXXBL




K776280WV-35-PTXXC

Current rating:7A AC/DC
额定电流: 7A AC/DC
Temperature range:-40℃~+85℃
温度范围: -40℃~+85℃

PART NO.:

K 776280 W V-35-PT SN W
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ①K:XKBTEK-Car Connector
- ②XKB Series No
- ③Category:W-Wafer
- ④Welding Board Range:V-Stright 180°
- ⑤Row No.Pin No:35 Pin
- ⑥Material:PT-PBT
- ⑦Palting:V01-Gold Flash ;SN-Plated Tin
- ⑧Color:X:B-Black; W-White; GY-Gray; BL-Blue;C-Orange



PLAYTING	COLOR	NAME
Gold Flash	Orange	K776280WV-35-PTV01C
Gold Flash	Blue	K776280WV-35-PTV01BL
Gold Flash	Gray	K776280WV-35-PTV01GY
Gold Flash	White	K776280WV-35-PTV01W
Gold Flash	Black	K776280WV-35-PTV01B
Plated Tin	Orange	K776280WV-35-PTSNC
Plated Tin	Blue	K776280WV-35-PTSNBL
Plated Tin	Gray	K776280WV-35-PTSNGY
Plated Tin	White	K776280WV-35-PTSNW
Plated Tin	Black	K776280WV-35-PTSNB

K776280WV-35-PTSNW	PBT	Brass	K776280H
PART NO	Material	Material(Pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

MODEL TYPE: 4.0mm Automobile connector		
PART NO.: K776280WV-35-PTSNW		
DWG NO.: X-K776280WV-35-PTSNW		
SCALE	PAGE	REVISION
N/A	1/1	A1