


1	2	3	4
---	---	---	---



- | Poles | Dimensions(mm) | | Poles | Dimensions(mm) | |
|-------|----------------|-------|-------|----------------|-------|
| | A | B | | A | B |
| 2 | 2.54 | 5.08 | 10 | 22.86 | 25.4 |
| 3 | 5.08 | 7.62 | 11 | 25.4 | 27.94 |
| 4 | 7.62 | 10.16 | 12 | 27.94 | 30.48 |
| 5 | 10.16 | 12.70 | 13 | 30.48 | 33.02 |
| 6 | 12.70 | 15.24 | 14 | 33.02 | 35.56 |
| 7 | 15.24 | 17.78 | 15 | 35.56 | 38.10 |
| 8 | 17.78 | 20.32 | | | |
| 9 | 20.32 | 22.86 | | | |

X2510WR-10-NOSN	Nylon 66 94V-0 UL	Brass	Tin-Plated	X2510H
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERAuCES	

XKIB 星城 Connection

DESIGN	阿树	VIEW: 	MODEL TYPE: 2.54mm Crimp Style Connector		
CHECKED		UNIT: mm/in	PART NO.: X2510WR-10-N0SN		
APPROVED		SIZE: A4	DWG NO.: X-X2510WR-10-N0SN		
PRECISION CO., LIMITED			SCALE N/A	PAGE 1/1	REVISION A1