





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.24	阿树



PCB LAYOUT

Led Color	Part No	VR	IF	Recommended Operating	IF	
					Nom	Max
White	TM-005-D-01	DC5V	20mA	20mA	3.0V	3.6V
Red	TM-005-D-02	DC5V	20mA	20mA	1.7V	2.4V
Blue	TM-005-D-03	DC5V	20mA	20mA	3.0V	3.6V
Green	TM-005-D-04	DC5V	20mA	20mA	1.9V	2.4V
Yellow	TM-005-D-05	DC5V	20mA	20mA	1.9V	2.4V

7	LED	1		
6	Hat	1	ABS	Ag Plated
5	Terminal	4	Brass (0.30t)	
4	Contact	1	F.ag/SUS	
3	Base	1	PA66	
2	Cover	1	PET	
1	Keystake	1	PA66	
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树
CHECKED	
APPROVED	

VIEW:	
UNIT:	mm/in
SIZE:	A4

MODEL TYPE:	LED SWITCH
PART NO.:	TM-005-D-02
DWG NO.:	X-TM-005-D-02

SCALE	PAGE	REVISION
N/A	1/1	A1