






XKB



Specifications:

规格:

XKB

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:9A AC/DC

额定电流: 9A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25℃-+85℃

温度范围: -25℃-+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤10mΩ

接触电阻: ≤10mΩ

After environmental test:≤20mΩ

环境测试后: ≤20兆欧

X9357 W V X-2x08 B-N0 SN

01 02 03 04 05 06 07 08 09

01 Series No

02 Category:W-wafer

03 Welding Board Angle:V-180°

04 Welding Way: Blank-DIP

05 Row No.-Pin No: 2*xx-Double row

06 Special NO.

B-Arrange ushering with positioning column

07 Material:NO-PA66 94V-0:N2-PA66 94V-2

08 Planting Category:

V:All Gold-Plated;G:Gold-Plated Contact

S-SilverPlating;*01-Gold Flash;*02-2u";*03-3u"

*05-5u";10-10u";15-15u";*30-30u";*50-50u"

N-Plating Nickel 30u";SN-Bright tin plating 70u" SW-Fc

Tin plating

09 Color:Blank-natural color

Poles	Dimensions(mm)	
	A	B
2*07	25.20	40.00
2*08	33.60	48.40
2*09	46.20	61.00

X9357WV-2x08B-N0SN	Nylon 66 UL 94V-0	Phorphos Bronza	Tin-Plated	X9357HM-B
X9357WV-2x08B-N2SN	Nylon 66 UL 94V-2	Phorphos Bronza	Tin-Plated	X9357HM-B
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing

					XKB	DSND		DATE		SCALE: N/A	MODEL TYPE:
					ANGLAR	±5°	DWN		DATE	VIEW:	4.20 mm Crimp Style Connectors
ΔX					L≤4	±0.2	CHKD		DATE	UNIT: mm/in	PART NO.:
ΔX					4<L≤16	±0.3	APPD		DATE	SIZE: A4	X9357WV-2x08B-N0SN
ΔX					16<L≤63	±0.4					DWG NO.:
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L>63	±0.5					X-X9357WV-2x08B-N0SN
REVISIONS					UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT	SHEET
www.helloxkb.com										1.0g	1/1
										REVISION	
										A0	