REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	



规格 Specification:

1.额定值 Rating:3A 125/250VAC

2.接触电阻 Contact resistance:≤30 mΩ

3.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)

4.电气寿命 Electronics life:>10000 cycles

5.操作力 Operation force:500±200gf

6.所有材料符合Rohs要求 All meterials are Rohs compliant









PCB LAYOUT

PART NO.:

SS-	X	03	23	P	G-8	R	1	W	B
①	②	③	④	⑤	⑥	⑦	⑧	⑨	⑩	⑪

① SS: XKB Vertical handle;

② Enclosure Material:
A-Metal case;
BLANK-Plastic case;

③ Current Rating: 03-03A;

④ Switch Circuit:23-2P3T;

⑤ P: Welding plates;

⑥ Handle Shape: G-Camber handle

⑦ Handle Height: 3~15mm;

⑧ Enclosure Shape:R-Locking rings enclosure;

⑨ Terminal specs:
1:TYPE-1; 2:TYPE-2;
3:TYPE-3; 4:TYPE-4; 5:TYPE-5;

⑩ Handle Colour:
B-Black; W-White; R-Red

⑪ Housing Colour:
B-Black; W-White; R-Red



ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	桑 甚	VIEW:	MODEL TYPE: SLIDE SWITCH
CHECKED		UNIT: mm/in	PART NO.: SS-A0323PG-8R1WB
APPROVED		SIZE: A4	DWG NO.: X-SS-A0323PG-8R1WB

SCALE	PAGE	REVISION
N/A	1/1	A0