




PCB LAYOUT



Specifications:

规格:

Voltage rating: 250V AC/DC

额定电压: 250V AC/DC

Current rating: 3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage: 1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range: -40°C ~ +105°C

温度范围: -40°C ~ +105°C

Insulation resistance: ≥ 1000MΩ

绝缘电阻: ≥ 1000MΩ

Contact resistance: ≤ 20mΩ

接触电阻: ≤ 20mΩ

Material: PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category: 1U" Gold

镀层: 1U" Gold

Wave soldering temperature: 255 ± 5°C, 10S

波峰焊温度: 255 ± 5°C, 10S

X6521	F	V	- 2x24	- C85	D32
①	②	③	④	⑤	⑥

1. Series No

2. Category: F-Female

3. Welding Board Angle: V-Stright 180°

4. Row No. Pin No: 2xXX-2x01~2x40P

5. Plastic Height: C=8.5mm

6. Pin Length: D=3.2mm

X6521FV-2x24-C85D32	PA6T	Brass	X6521W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGULAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
ΔX					16 < L ≤ 63 ±0.4
ΔX					L > 63 ±0.5
REVISIONS					UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKLB

XKB INDUSTRIAL PRECISION CO., LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	2.54mm BTB Connector
CHKD	UNIT: mm/in	PART NO.: X6521FV-2x24-C85D32
APPD	SIZE: A4	DWG NO.: X-X6521FV-2x24-C85D32
		WEIGHT
		SHEET 1/1
		REVISION A0