








REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		料号变更, 图面升级整理图面	2025.06.04	阿树
A2	N/A		模具更新	2025.07.30	阿树



Specifications(规格):

- 1.Rated electrical load(额定电压): 30V 0.5A
- 2.Contact resistance(接触电阻): ≤30mΩ Max
- 3.Insulation resistance(绝缘电阻): ≥100MΩ(DC250V) Min
- 4.Withstanding voltage(耐压值): AC500V(50Hz)min;
- 5.Insertion and extraction force(插拔力): 3~30N
- 6.Mating cycles(使用寿命): 3000 cycles Min

9	Cover	1	PBT(4815)	Black
8	Pedestal	1	PBT(4815)	Black
7	Terminal 7	1	Phosphor bronze	Ag-Plated
6	Terminal 6	1	Brass(0.30t)	Ag-Plated
5	Terminal 5	1	Phosphor bronze	Ag-Plated
4	Terminal 4	1	Brass(0.30t)	Ag-Plated
3	Terminal 3	1	Phosphor bronze	Ag-Plated
2	Terminal 2	1	Phosphor bronze	Ag-Plated
1	Terminal 1	1	Phosphor bronze	Ag-Plated
NO	NAME	QTY	MATERIAL	Remark

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	3.5 PHONE JACK
APPROVED		SIZE: A4	PART NO.: PJ-3262
			DWG NO.:
SCALE	PAGE	REVISION	
N/A	1/1	A1	

XKB INDUSTRIAL PRECISION CO.,LIMITED