


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		INITIAL RELEASE	/	/
A2	N/A		图面升级整理图面	2025.06.19	阿树

SPECIFICATIONS 规范:

1. ELECTRICAL CHARACTERISTICS 电气特性:

- 1.1. RATING 电流: 3A;
- 1.2. CONTACT RESISTANCE 接触电阻: 30 mΩ MAX.(INITIAL);
- 1.3. DIELECTRIC WITHSTANDING 耐电压: 100V AC MIN.;
- 1.4. INSULATION RESISTANCE 绝缘电阻: 100MΩ MIN.;
2. DURABILITY 使用寿命: 10,000 CYCLES MIN.;
3. INSERTION FORCE 插入力: 5~20N;
4. EXTRACTION FORCE 拔出力: 6~20N;
5. WATER PROOFNESS 水密性: THIS PRODUCT IS BASED ON IPX7 / IPX6.
6. PLUG INTERFACE DIMENSIONS CONFORM TO USB2.0 SPEC.
7. PACKAGING: TAPE & REEL.



U262-061N-4BFC10

1:0.8u"
2:5u"
3:10u"
4:3u"
W:WHITE
B:BLACK
1:PBT
2:PA6T
3:PA9T
4:LCP

A5	CC1	B12	GND
A9	VBUS	B9	VBUS
A12	GND	B5	CC2
PIN	SIGNAL NAME	PIN	SIGNAL NAME

3	Shell	1	SUS304R-1/2H Ni
2	Contact	6	Plating: 0.25mm Phosphor bronze C5191R-EH Au/Ni Plating T=0.20mm
1	Housing	1	PA10T (G.F30%%)
NO.	PART NAME	QTY	FINISH

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	Type-C 3.1
CHECKED		UNIT:	mm/in	PART NO.:	U262-061N-4BFC10
APPROVED		SIZE:	A4	DWG NO.:	X-U262-061N-4BFC10

SCALE	PAGE	REVISION
N/A	1/1	A1