





Y型端子




14P-64P 双槽




6P 小鼻/无槽

TYPE C




6P 大鼻/无槽

TYPE A




8P 大鼻/无槽

TYPE A




6P 小鼻/单槽

TYPE B



8P 小鼻/单槽

TYPE B



10P-12P 单槽

Blank


接触电阻: $\leq 20\text{m}\Omega$ MAX

①	②	③	④	⑤	⑥
---	---	---	---	---	---

6.Plating:V01-Gold Flash

X9555H2-2x13-PTV01	PBT	BRASS	Gold Flash	X9555WV-2xXX	XPD1.27-A28PXX-1DC	X9555H-2xXXA
				X9555WR-2xXX		X9555H-2xXXB
				X9555WV/S-2xXX		X9555H-2xXXC
				X9555WV-2xXX		X9555H-2xXXA
				X9555WR-2xXX		X9555H-2xXXB
X9555H2-2x13-PTV01				X9555WV/S-2xXX		X9555H-2xXXC
PART NO	Material	Material(pin)	Finish(pin)	Suitable XGB Wafer	Suitable XGB flat cable	Suitable XGB DIP

NUMBER OF POSITIONS	DIMENSION			NUMBER OF POSITIONS	DIMENSION		
	A	B	C		A	B	C
2x03	12.32	5.08	1.9	2x13	37.72	30.48	3.8
2x04	14.86	7.62	小1.9/大3.8	2x15	42.80	35.56	3.8
2x05	17.40	10.16	3.8	2x17	47.88	40.64	3.8
2x06	19.94	12.70	3.8	2x18	50.42	43.18	3.8
2x07	22.48	15.24	3.8	2x20	55.50	48.26	3.8
2x08	25.02	17.78	3.8	2x22	60.58	53.34	3.8
2x09	27.56	20.32	3.8	2x25	68.20	60.96	3.8
2x10	30.10	22.86	3.8	2x30	80.90	73.66	3.8
2x11	32.64	25.40	3.8	2x32	85.98	78.74	3.8
2x12	35.18	27.94	3.8				

								DSND		SCALE: N/A	MODEL TYPE: 2.54mm IDC		
Δ X					ANGLAR	±5°		DWN		VIEW: 	PART NO.: X9555H2-2x13-PTV01		
Δ X					4<L≤ 16	±0.3		CHKD		UNIT: mm/in	DWG NO.: X-X9555H2-2x13-PTV01		
Δ X					16<L≤ 63	±0.4		APPD		SIZE: A4			
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5							
REVISIONS								UNSPECIFIED TOLERANCES					
www.helloxb.com www.helloxb.cn www.xk-da.cn							KXB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT	SHEET 1/1	REVISION A0	