


Specifications:

规格:

Voltage rating:100V AC/DC

额定电压: 100V AC/DC

Current rating:1.5A AC/DC

额定电流: 1.5A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥500MΩ

绝缘电阻: ≥500MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

X1515 W R S-2x09-LP SW
① ② ③ ④ ⑤ ⑥ ⑦

1.Series No

2.Category:W-Wafer


3.Welding Board Angle:R-Stright 90°

4.Welding Way:S-SMT


5.Row No.Pin No:2xXX-2x04~2x14P

6.Material:LP-LCP 94V-0 (Natural)




7.Plating:SW- Matte Tin Plated



2x04Pin / 2x05Pin With Mylar



2x04Pin
2x05Pin



Recommended PCB Layout
Tolerance:±0.05

Poles	Dimensions(mm)			
	A	B	C	D
2x04	5.25	10.30	7.40	8.95
2x05	6.25	11.80	8.90	10.45
2x06	7.25	13.30	10.40	11.95
2x07	8.25	14.80	11.90	13.45
2x08	9.25	16.30	13.40	14.95
2x09	10.25	17.80	14.90	16.45
2x10	11.25	19.30	16.40	17.95
2x11	12.25	20.80	17.90	19.45
2x12	13.25	22.30	19.40	20.95
2x13	14.25	23.80	20.90	22.45
2x14	15.25	25.30	22.40	23.95

X1515WRS-2x09-LPSW	LCP	Phosphor Bronze	X1515H-A
PART NO	Material	Material(Pin)	Suitable XKB Housing

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

DSND		SCALE: N/A	MODEL TYPE: 1.5mm Crimp Style Connector	
DWN		VIEW:	PART NO.: X1515WRS-2x09-LPSW	
CHKD		UNIT: mm/in	DWG NO.: X-X1515WRS-2x09-LPSW	
APPD		SIZE: A4	WEIGHT	SHEET 1/1
XKB INDUSTRIAL PRECISION CO.,LIMITED			REVISION A0	