



	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	桑 甚






规格 Specification:

- 1.额定值 Rating:3A 125/250VAC
- 2.接触电阻 Contact resistance: $\leq 30\text{ m}\Omega$
- 3.绝缘电阻 Insulation resistance: $\geq 100\text{ M}\Omega$ (DC500V/Min)
- 4.电气寿命 Electronics life: $> 10000\text{ cycles}$
- 5.操作力 Operation force: $500\pm 150\text{ gf}$
- 6.所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:


$$\frac{\text{SS-X}}{\textcircled{1}} \quad \frac{\text{03}}{\textcircled{2}} \quad \frac{\text{22}}{\textcircled{3}} \quad \frac{\text{S}}{\textcircled{4}} \quad \frac{\text{G-7}}{\textcircled{5}} \quad \frac{\text{R}}{\textcircled{6}} \quad \frac{\text{4}}{\textcircled{7}} \quad \frac{\text{B}}{\textcircled{8}} \quad \frac{\text{B}}{\textcircled{9}}$$

- ① SS: XKB Vertical handle;
- ② Enclosure Material:
A—Metal case;
BLANK—Plastic case;
- ③ Current Rating: 03—3A;
- ④ Switch Circuit: 22—2P2T;
- ⑤ S: Wire bonding;
- ⑥ Handle Shape: G—Camber handle;
- ⑦ Handle Height: 3~15mm;
- ⑧ Enclosure Shape: R—Locking rings enclosure;
- ⑨ Terminal specs:
1: TYPE-1; 2: TYPE-2; 3: TYPE-3;
4: TYPE-4; 5: TYPE-5;
- ⑩ Handle Colour:
B—Black; W—White; R—Red
- ⑪ Housing Colour:
B—Black; W—White; R—Red



产品字码标识

ANGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	桑 菴	VIEW: 	MODEL TYPE: SLIDE SWITCH		
CHECKED		UNIT: mm/in	PART NO.: SS-0322SG-7R4BB		
APPROVED		SIZE: A4	DWG NO.: X-SS-0322SG-7R4BB		
PRECISION CO.,LIMITED			SCALE	PAGE	REVISION
			N/A	1 / 1	Δ0