

Specifications:

规格:

Voltage rating: 3A 250V AC/DC

额定电压: 3A 250V AC/DC

Temperature range:-40℃~+105℃

温度范围: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$

Insulator: PA66 UL 94V-0 Nature

绝缘材料: PA66 UL 94V-0 Nature

Terminal: Phosphor Bronze

端子: Phosphor Bronze

X2514 H I - 06 L - 0 - 0A

① ② ③ ④ ⑤ ⑥ ⑦

①Series No.

②Category: H-HSG

③Welding Board Angle: I-HSG+hardware

④Row No.-Pin No.: XX-Single row


⑤L : With Lock

⑥0=Tin plated 120~200u" over Ni 30u" overall,for AWG#22~#24

1=Tin plated 120~200u" over Ni 30u" overall,for AWG#26.

G=Gold Flash over Ni 80~150u" overall.

⑦See the Table of next page



PCB LAYOUT

$$A = 2.5 \times (\text{No. of circuit} - 1)$$
$$B = A + 5.0$$

X2514HI-06L-0-0A	PA66 94V-0	AWG #22-#24 AWG #26	Phosphor Bronze	X2514W
PART NO	Material	Wire Range	Material (Terminal)	Suitable XKB Wafer

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.5 mm IDC Style Connectors						
Δx					ANGLAR	$\pm 5^{\circ}$	DWN		DATE		VIEW: 	PART NO.: X2514HI-06L-0-0A						
Δx					$L \leq 4$	± 0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-2514HI-06L-0-0A						
Δx					$4 < L \leq 16$	± 0.3	APPD		DATE		SIZE: A4							
Δx					$16 < L \leq 63$	± 0.4	XKB INDUSTRIAL PRECISION CO.,LIMITED											
MARK	DESCRIPTION			DATE	REVISED	APPROVED							X2514HI-06L-0-0A					
REVISIONS													X-2514HI-06L-0-0A					
							UNSPECIFIED TOLERANCES											
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn							WEIGHT SHEET REVISION											
							1.0g 1/1 A0											