





1		2		3			4		
30.00 [1.181]				REVISIONS					
				REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
				A0	N/A		INITIAL RELEASE	2024.05.09	




规格 Specification:

- 额定值 Rating: 3A 125/250VAC
- 接触电阻 Contact resistance: $\leq 30\text{ m}\Omega$
- 绝缘电阻 Insulation resistance: $\geq 100\text{ M}\Omega$ (DC500V/Min)
- 电气寿命 Electronics life: > 10000 cycles
- 操作力 Operation force: $400 \pm 150\text{ gf}$
- 所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:

SS-X 03 25 P G-9 N 3 W W
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- ① SS: XKB Vertical handle;
- ② Enclosure Material:
A-Metal case;
BLANK-Plastic case;
- ③ Current Rating: 03-03A;
- ④ Switch Circuit: 25-2P5T;
- ⑤ P: Welding plates;
- ⑥ Handle Shape: G-Camber handle;
- ⑦ Handle Height: 3~15mm;
- ⑧ Enclosure Shape: N-Square enclosure;
- ⑨ Terminal specs:
1: TYPE-1; 2: TYPE-2;
3: TYPE-3; 4: TYPE-4; 5: TYPE-5;
- ⑩ Handle Colour:
B-Black; W-White; R-Red
- ⑪ Housing Colour:
B-Black; W-White; R-Red



产品字码标识

ANGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	桑 葚	VIEW:	MODEL TYPE: SLIDE SWITCH		
CHECKED		UNIT: mm/in	PART NO.: SS-0325PG-9N3WW		
APPROVED		SIZE: A4	DWG NO.: X-SS-0325PG-9N3WW		
XKB INDUSTRIAL PRECISION CO., LIMITED			SCALE	PAGE	REVISION
			N/A	1/1	A0