



	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		新增卡扣R角, 增强卡扣强度	2024.03.14	桑 葦



ANGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



3D VIEW

XXLE

XKB INDUSTRIAL PRECISION CO.,LIMITED

Specifications (规格):

1. Voltage rating(额定电压):250V AC DC
2. Current rating(额定电流):5.0A AC/DC
3. Withstanding voltage(耐压值): $\geq 1500\text{V AC/minute}$
4. Insulation resistance(绝缘电阻): $1000\text{M}\Omega$ Min
5. Contact resistance(接触电阻): $20\text{m}\Omega$ Max
6. Temperature range(使用温度):- $25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

PART NO.:

X3025 H M-2x08 N2
① ② ③ ④ ⑤

- ① Series No
- ② Category:H-Housing
- ③ Welding Board Angle:M-Male Housing
- ④ Row No-Pin: 2x01-2x12P
- ⑤ Material:N2-PA66, UL 94V-2, BLACK

X3025HM-2x08-N2	PA66 94V-2	BLACK	X3025W	X3025TF
PART NO.	MATERIAL	COLOR	Suitable XKB Wafer	Suitable XKB Terminal

MODEL TYPE: 3.0mm Crimp Style Housing			
PART NO.: X3025HM-2x08-N2			
DWG NO.: X-X3025HM-2x08-N2			
SCALE	PAGE	REVISION	
N/A	1/1	A0	