




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图框升级整理图面	2024.07.31	阿 树



- SPECIFICATIONS
- Voltage rating:600V AC/DC
 - Current rating:9A AC/DC
 - Withstanding Voltage:1500V AC/minute
 - Temperature range:-45°C+125°C
 - Insulation resistance: $\geq 1000M\Omega$
 - Contact resistance: $\leq 10m\Omega$
 - After environmental testing: $\leq 20m\Omega$

PART NO.:
X9357 W V-06-XX N2 SN XX
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series No
② Category:W-Wager
③ Welding Board Angle:V-Straight 180°
④ Row No.Pin No:XX-02~06 P
⑤ Special No: Blank-DIP
⑥ Material:N2-PA66 94V-2
⑦ Plating Category:SN-Bright tin plating
⑧ Color:Blank-natural color

Poles	Dimensions(mm)	
	A	B
02	4.20	9.60
03	8.40	13.80
04	12.60	18.00
05	16.80	22.20
06	21.00	26.40

X9357WV-06-N2SN	Nylon 66 UL 94V-2	Brass	Tin-Plated	X9357H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

ANGULAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿 树	VIEW:		MODEL TYPE: 4.20 mm Crimp Style Connectors
CHECKED		UNIT:	mm/in	PART NO.: X9357WV-06-N2SN
APPROVED		SIZE:	A4	DWG NO.: X-X9357WV-06-N2SN

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1