


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.19	阿树




Technical Data
 Pin(outer sleeve):Brass,machined CuZn38Pb2
 Insulator:PPS UL94V-0 colour:black
 Current rating:3Amps
 Mating pin ϕ :0.60mm
 Contact resistance:max 10m Ω
 Dielectric strength:min 1000V RMS
 Operaling temperature:-40°C~+105°C
 Soldering temperature:+255°C

PART NO.:

X5511 W V-40 -C396 D43-1220
 ① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
- ②Category:W-Wafer
- ③Welding Board Angle:V-Straight 180°
- ④Row No-Pin No:XX-01P-XXP
- ⑤Pin Length :C=3.96mm
- ⑥Pin Length :D=4.3mm
- ⑦1220:Type1220



X5511WV-40-C396D43-1220	PPS 94V-0	Brass	Tin Gold 1u"	X5511F
PART NO	Material	Material(Pin)	Finish(Terminal)	Mates With XKB Pin Header

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCE	



DESIGN	阿树	VIEW:		MODEL TYPE:	2.54mm BTB Style Connector
CHECKED		UNIT:	mm/in	PART NO.:	X5511WV-40-C396D43-1220
APPROVED		SIZE:	A4	DWG NO.:	X-X5511WV-40-C396D43-1220
			SCALE	PAGE	REVISION
			N/A	1/1	A1