









P.C.B Layout



Rating: 0.5A 30V DC  
Contact Resistance:  $\leq 0.03\Omega$   
Insulation resistance:  $\geq 100M\Omega$   
Operating temperature:  $-30^{\circ}\text{C} \sim 70^{\circ}\text{C}$   
Operating force: 3-30N  
Operating Life: 5,000cycles



|                |           |         |            |                 |                                                                                       |              |
|----------------|-----------|---------|------------|-----------------|---------------------------------------------------------------------------------------|--------------|
| ②              | Terminal  | ——      | 4          | Phosphor bronze | Ag Plating                                                                            | ——           |
| ①              | Housing   | ——      | 1          | PPA             | Black                                                                                 | ——           |
| ITEM           | PART NAME | TER'NO. | QTY.       | MATERIAL        | FINISHING                                                                             | REMARK       |
| APPROVALS      |           |         | DATE       |                 |  |              |
| DRAWN          |           | LIANG   | 2026.07.29 |                 |                                                                                       |              |
| CHECKED        |           |         |            | TITLE:          | PHONE JACKES                                                                          |              |
| APPROVALS      |           |         |            | PART NO.        | PJ-328-5A                                                                             |              |
| TOLERANCES ARE |           | 30~以上   | ±0.30      | ANGLE           | UNIT: mm                                                                              | SCALE: 1:1   |
|                |           | 10~30   | ±0.20      |                 |                                                                                       |              |
|                |           | 5~10    | ±0.15      |                 |                                                                                       |              |
|                |           | ~ 5     | ±0.10      |                 |                                                                                       |              |
|                |           | ±2°     |            | DRAWING NO.     | ——                                                                                    | SHEET 1 OF 1 |

|         |      |       |              |         |        |        |
|---------|------|-------|--------------|---------|--------|--------|
| ECN NO. | REV. | DATE. | DESCRIPTION. | CHANGE. | CHECK. | APPRO. |
|         | A    |       | NEW          |         |        |        |