

规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗: Contact Resistance
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:
1000MEGA ohms MIN

物理性能: Mechanical:

1. 插拔力: Connector Mate and Unmate Force
Mate force: 3.57kgf(MAX)
Unmate force: 1.02kgf(MIN)
2. 端子保持力: Terminal Retention
1.0kgf(MIN)

原材料: Material:

1. 塑胶: Housing:
Hing Temperature Tthermaplastics,

2. 端子: Contact: Copper Alloy C2680

3. 外壳: Shell: Copper Alloy C2680/SPCC

电镀: Finish:





1. 端子: Contact: Plated Gold in Mating Area;
Tin On Solder Talls

端子四周镀50U”(MIN)锡, 镀金区域镀100—200U”镀金1U”

2. 外壳: Shell:

铜壳四周镀80U”(MIN)锡

Nickel Plating



- 1 VCC
- 2 D+
- 3 D-
- 4 GND

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD					
CHECKED:	DATE:	TITLE: USB-A/F-1*4P H=10.0mm 180度插板 铁壳 鱼叉脚 无卷边					
DRAWN: SXA	DATE: 2019-06-18	PROD. P/N	U-USBAS04P-F005				
		UNIT	mm	SCALE	free	⊕	≡
		FILE NO.	Ckmtw-USB-00078	REV.	A	HLW	W