

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PBT+30%G.F UL94V-0, 颜色: 黑色.

Housing: PBT+30%G.F UL94V-0, Color: Black

四方针: 青铜, 镍底30u"MIN, 表面镀金3u"MIN

Contact: Bronze, 3u"MIN GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Raring Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.





Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C



Ordering Information

P125-12 12 A4 A S 116 A 1

HEIGHT OF HOUSING	NO. OF PINS PER ROW	Contact Plating	INSULATOR MATERIAL:	LENGTH OF TERMINAL	PACKING
15: 1.5mm	2~40P	Full of Gold	A: PBT	OF	A: PE Bag
17: 1.7mm		Semi-gold	B: PA6T	TERMINAL	B: Tape & Reel
20: 2.0mm			C: PA9T		C: Tube
25: 2.54mm			D: LCP		D: Tube+CAP
30: 3.0mm					E: Tray

RoHS COMPLIANT

客编:

1. 带*为品质重点检验尺寸

注意事项

				OPERATION		SCALE		Fit		Yxcon 东莞市宇熙精密连接器有限公司			
				X.X	±0.25	UNIT		MM		www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.			
				X.XX	±0.20	SIZE	A4	DESIGN		李官淼2021.09.14		PART NO	P125-1212A4AS116A1
				X.XXX	±0.10	SHEET		CHECK				TI TLE:	2.54排针 2*12P L=11.6/3.0 180度
				Angle	±3°	PROJ.		APPROVE				Cust omer No.	PBT 镀3U金
				DI M	TOL								