




技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. 额定电压: 50V, AC.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 100\text{M}\Omega$

序号	品名	材质
①	0.5 Pitch C型单槽立式 BTB公座底座	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch C型单槽立式 BTB公座端子	铜合金/表面点镀金

Part No	CKT	A	B	C
BX-BTB0.5-13HGC2-10PLT	2X5	2.00	3.40	5.50
BX-BTB0.5-13HGC2-12PLT	2X6	2.50	3.90	6.00
BX-BTB0.5-13HGC2-14PLT	2X7	3.00	4.40	6.50
BX-BTB0.5-13HGC2-16PLT	2X8	3.50	4.90	7.00
BX-BTB0.5-13HGC2-18PLT	2X9	4.00	5.40	7.50
BX-BTB0.5-13HGC2-20PLT	2X10	4.50	5.90	8.00
BX-BTB0.5-13HGC2-22PLT	2X11	5.00	6.40	8.50
BX-BTB0.5-13HGC2-24PLT	2X12	5.50	6.90	9.00
BX-BTB0.5-13HGC2-26PLT	2X13	6.00	7.40	9.50
BX-BTB0.5-13HGC2-28PLT	2X14	6.50	7.90	10.00
BX-BTB0.5-13HGC2-30PLT	2X15	7.00	8.40	10.50
BX-BTB0.5-13HGC2-32PLT	2X16	7.50	8.90	11.00
BX-BTB0.5-13HGC2-34PLT	2X17	8.00	9.40	11.50
BX-BTB0.5-13HGC2-36PLT	2X18	8.50	9.90	12.00
BX-BTB0.5-13HGC2-38PLT	2X19	9.00	10.40	12.50
BX-BTB0.5-13HGC2-40PLT	2X20	9.50	10.90	13.00
.....	...	...	...	...
BX-BTB0.5-13HGC2-100PLT	2X50	24.50	25.90	28.00

合高(H)	公座单高	母座单高	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-BTB0.5-13HGC2-XPLT		版本 REV.	A
						X.: ±0.50	±1°	审核 CHECK	EVA	品名 TITLE	0.5 Pitch C型单槽立式BTB公座(单高1.3)	页次 SHEET	1/1			
2.0	1.3	1.9				X.X: ±0.20		核准 APPROVAL	JADE	客户料号 CUTM.NO.	 Bossie (博锡)					
2.5	1.3	2.4				X.XX:±0.10		单位 UNITS	MM	比例 SCALE						1:1
1	2	3		4	5		6		7	8	9					