







技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40°C~85°C.
3. 额定电压: 50V, AC.
4. 接触电阻: ≤0.02Ω.
5. 绝缘电阻: ≥100MΩ

序号	品名	材质
①	0.5 Pitch C型单槽 立式BTB母座胶芯	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch C型单槽 立式BTB母座端子	铜合金/表面点镀金

Part No	CKT	A	B	C
BX-BTB0.5-14HMC2-10PLT	2X5	2.00	3.40	5.50
BX-BTB0.5-14HMC2-12PLT	2X6	2.50	3.90	6.00
BX-BTB0.5-14HMC2-14PLT	2X7	3.00	4.40	6.50
BX-BTB0.5-14HMC2-16PLT	2X8	3.50	4.90	7.00
BX-BTB0.5-14HMC2-18PLT	2X9	4.00	5.40	7.50
BX-BTB0.5-14HMC2-20PLT	2X10	4.50	5.90	8.00
BX-BTB0.5-14HMC2-22PLT	2X11	5.00	6.40	8.50
BX-BTB0.5-14HMC2-24PLT	2X12	5.50	6.90	9.00
BX-BTB0.5-14HMC2-26PLT	2X13	6.00	7.40	9.50
BX-BTB0.5-14HMC2-28PLT	2X14	6.50	7.90	10.00
BX-BTB0.5-14HMC2-30PLT	2X15	7.00	8.40	10.50
BX-BTB0.5-14HMC2-32PLT	2X16	7.50	8.90	11.00
BX-BTB0.5-14HMC2-34PLT	2X17	8.00	9.40	11.50
BX-BTB0.5-14HMC2-36PLT	2X18	8.50	9.90	12.00
BX-BTB0.5-14HMC2-38PLT	2X19	9.00	10.40	12.50
BX-BTB0.5-14HMC2-40PLT	2X20	9.50	10.90	13.00
.....	...	...	...	...
BX-BTB0.5-14HMC2-100PLT	2X50	24.50	25.90	28.00



合高(H)	公座单高	母座单高	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE	制图 DRAWING	EMMA	料号 PART NO.	BX-BTB0.5-14HMC2-XPLT	版本 REV.	A
1.5	1.3	1.4				X.: ±0.50 ±1°	审核 CHECK	EVA	品名 TITLE	0.5 Pitch C型单槽立式BTB母座(单高1.4)	页次 SHEET	1/1
2.0	1.3	1.9				X.X: ±0.20	核准 APPROVAL	JADE	客户料号 CUTM.NO.			
2.5	1.3	2.4				X.XX: ±0.10	单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)	