








技术指标:


1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。

High photosynthesis 合高 (H)	The female seat neight 母座单高 (H1)	The male seat neight 公座单高 (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90



序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-BTB0.5-35HMA1-XPLT	版本 REV.	A
①	0.5 Pitch双槽立式BTB母座胶芯	PA10T UL94 V-0 颜色:黑色				X.: ± 0.50	$\pm 1^{\circ}$	审核 CHECK	EVA		品名 TITLE	0.5 Pitch双槽立式BTB母座(单高3.5)	页次 SHEET	1/2
②	0.5 Pitch双槽立式BTB母座端子	铜合金/表面点镀金				X.X: ± 0.20		核准 APPROVAL	JADE		客户料号 CUTM.NO.			
③	0.5 Pitch双槽立式BTB母座吸盖	LCP UL94 V-0 颜色:黑色.				X.XX: ± 0.10		单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)		

PIN NO	PIN	DIM A	DIM B	DIM C	DIM D	DIM E
BX-BTB0.5-35HMA1-8PLT	8	1.50	2.55	4.70	3.40	4.00
BX-BTB0.5-35HMA1-10PLT	10	2.00	3.05	5.20	3.90	
BX-BTB0.5-35HMA1-12PLT	12	2.50	3.55	5.70	4.40	
BX-BTB0.5-35HMA1-14PLT	14	3.00	4.05	6.20	4.90	
BX-BTB0.5-35HMA1-16PLT	16	3.50	4.55	6.70	5.40	
BX-BTB0.5-35HMA1-18PLT	18	4.00	5.05	7.20	5.90	
BX-BTB0.5-35HMA1-20PLT	20	4.50	5.55	7.70	6.40	
BX-BTB0.5-35HMA1-22PLT	22	5.00	6.05	8.20	6.90	
BX-BTB0.5-35HMA1-24PLT	24	5.50	6.55	8.70	7.40	
BX-BTB0.5-35HMA1-26PLT	26	6.00	7.05	9.20	7.90	
BX-BTB0.5-35HMA1-28PLT	28	6.50	7.55	9.70	8.40	
BX-BTB0.5-35HMA1-30PLT	30	7.00	8.05	10.20	8.90	
BX-BTB0.5-35HMA1-32PLT	32	7.50	8.55	10.70	9.40	
BX-BTB0.5-35HMA1-34PLT	34	8.00	9.05	11.20	9.90	
BX-BTB0.5-35HMA1-36PLT	36	8.50	9.55	11.70	10.40	8.00
BX-BTB0.5-35HMA1-38PLT	38	9.00	10.05	12.20	10.90	
BX-BTB0.5-35HMA1-40PLT	40	9.50	10.55	12.70	11.40	
BX-BTB0.5-35HMA1-44PLT	44	10.50	11.05	13.70	12.40	
BX-BTB0.5-35HMA1-50PLT	50	12.00	13.05	15.20	13.90	
BX-BTB0.5-35HMA1-60PLT	60	14.50	15.55	17.70	16.40	
BX-BTB0.5-35HMA1-70PLT	70	17.00	18.05	20.20	18.90	
BX-BTB0.5-35HMA1-80PLT	80	19.50	20.55	22.70	21.40	
BX-BTB0.5-35HMA1-100PLT	100	24.50	25.55	27.70	26.40	

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-BTB0.5-35HMA1-XPLT	版本 REV.	A
			X.: ±0.50	±1°		EVA			品名 TITLE	0.5 Pitch双槽立式BTB母(单高3.5)	页次 SHEET	2/2
			X.X: ±0.20			JADE			客户料号 CUTM.NO.			
			X.XX: ±0.10			核准 APPROVAL			Bossie (博锡)			
					单位 UNITS	MM	比例 SCALE	1:1				